



# Einhell

**EXPERT Plus**

## TE-CL 18 Li H-Solo

### Cordless Light

Item No.: 4514130

Ident No.: 11015

Bar Code: 4006825610451

The TE-CL 18 Li H- solo rechargeable lamp provides plenty of light when you are working in the dark or in areas with poor lighting. It is equipped with a high-performance LED for extra bright light with 280 lm. Thanks to its low power consumption, the lamp provides prolonged lighting. Optimum illumination is assured by the flexibly swiveling lamp head. The rugged housing with carry handle and soft grip make the lamp very easy to transport. Also, it can be hung up quickly and easily anywhere by means of the practical metal hook. The TE-CL 18 Li H-solo rechargeable lamp is a member of the Einhell Power X-Change family and can be powered by all batteries from other Power X-Change family products. Supplied without a battery and charger.

### Features

- High-quality LED of the company CREE Ltd.
- Practical metal hooks
- Ergonomic handle with soft grip
- A member of the Power X-Change family
- High flexibility thanks to a swiveling head
- Supplied without battery and charger (available separately)

### Technical Data

- Accumulator 18 V | Li-Ion
- Number of LED 1 Pieces
- Luminous flux 280 lm

### Logistic Data

- Product weight 0.22
- Gross weight single packaging 0.3
- Dimensions single packaging 80 x 75 x 243 mm
- Pieces per export carton 8 Pieces
- Gross weight export carton 2.9 kg
- Dimensions export carton 325 x 263 x 195 mm
- Container quantity (20"/40"/40"HC) 12400 | 25600 | 0

