

Printed-circuit board connector - PTF 0,3/ 4-WB-10-H - 1707565

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Plug component, Nominal current: 10 A, Rated voltage (III/2): 24 V, Number of positions: 4, Pitch: 2.4 mm, Color: white, Contact surface: Tin, Mounting: Direct plug-in method, Length of the punched-on cables: 500 mm, for flexible PCBs with a width of 10 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

Why buy this product

- The small size enables connection even in applications where space is limited
- Easy connection of the PCB saves time
- According to IEC 60838-2-2
- The tight fit on the PCB and high current carrying capacity create a safe connection



Key Commercial Data

Packing unit	20 pc
Minimum order quantity	20 pc
GTIN	 4 046356 934183
Weight per Piece (excluding packing)	18.81 g
Country of origin	Germany

Technical data

Dimensions

Length	9 mm
Height	4.8 mm
Width	11.2 mm
Pitch	2.40 mm

General

Range of articles	PTF 0,3/...-WB-H
Type of contact	Female connector
Number of positions	4
Insulating material group	IIIa
Rated voltage (III/2)	24 V

Printed-circuit board connector - PTF 0,3/ 4-WB-10-H - 1707565

Technical data

General

Nominal current I _N	10 A
Nominal cross section	0.34 mm ²
Maximum load current	10 A (Total current of all contacts)
Insulating material	PBT
Flammability rating according to UL 94	V0

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 5.1	27141190
eCl@ss 6.0	27141190
eCl@ss 8.0	27440402
eCl@ss 9.0	27440402

ETIM

ETIM 4.0	EC002643
ETIM 5.0	EC002643

Approvals

Approvals


Approvals

UL Recognized / EAC

Ex Approvals

Approvals submitted

Approval details

UL Recognized 	
mm ² /AWG/kcmil	22
Nominal current I _N	5 A

Printed-circuit board connector - PTF 0,3/ 4-WB-10-H - 1707565

Approvals

Nominal voltage UN	60 V
--------------------	------

EAC

Accessories

Additional products

Printed-circuit board connector - PTF 0,3/ 2-WB-10-H - 1707562




Plug component, Nominal current: 10 A, Rated voltage (III/2): 24 V, Number of positions: 2, Pitch: 2.4 mm, Color: white, Contact surface: Tin, Mounting: Direct plug-in method, Length of the punched-on cables: 500 mm, for flexible PCBs with a width of 10 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

Printed-circuit board connector - PTF 0,3/ 4-BB-10-H - 1707563



Plug component, Nominal current: 10 A, Rated voltage (III/2): 24 V, Number of positions: 4, Pitch: 2.4 mm, Color: white, Contact surface: Tin, Mounting: Direct plug-in method, for flexible PCBs with a width of 10 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

PCB - PTF 0,3/ 4-FLEX-I-10 - 1848503



Accessories, Number of positions: 4, Pitch: 2.4 mm, Mounting: PCB connector

PCB - PTF 0,3/ 4-FLEX-L-10 - 1848516



Accessories, Number of positions: 4, Pitch: 2.4 mm, Mounting: PCB connector

Printed-circuit board connector - PTF 0,3/ 4-WB-10-H - 1707565

Accessories


PCB - PTF 0,3/ 4-FLEX-T-10 - 1848529

Accessories, Number of positions: 4, Pitch: 2.4 mm, Mounting: PCB connector




Drawings

Drilling diagram



Diagram



Type: PTF 0,3/ 4-WB-10-H

Dimensional drawing

