

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002091119](#)
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-1190-003 \(PDF\)](#)
[Product Specification PS-43660-9999 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	1381
Application	Power
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	Standard .093" Pin and Socket Connectors
Packaging Alternative	02-09-1117 (Reel)
Product Name	Standard .093"
UPC	800753746077

Physical


Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.360/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22
Wire Size mm²	N/A

Material Info

Old Part Number [1381-A\(P901\)L](#)

Reference - Drawing Numbers

Packaging Specification	PK-1190-003
Product Specification	PS-43660-9999
Sales Drawing	SD-1381-*



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[1381](#) Series

Use With

[1619](#) Plug or Receptacle Housing,
[1545](#) Plug or Receptacle Housing, [1396](#)
Plug or Receptacle Housing, [1490](#) Plug
or Receptacle Housing, [2629](#) Plug or
Receptacle Crimp Housings, [1261](#) Plug or
Receptacle Housing, [1292](#) Plug or Recept

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Insertion Tool	0011020003
Extraction Tool	0011030006

Hand Crimp Tool	<u>0638191200</u>
Extractor Tool	<u>0638240200</u>
for .093 and	
HCS-125 Product	
Series	

This document was generated on 08/03/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION