

6000/9000 Series  
**INTEGRA SERIES**



**DIMENSIONS**

**SEAT**  
20" W x 18" D  
3" Thick

**MEDIUM BACK**  
17 1/2" W x 16" H  
3" Thick


**LARGE BACK**  
17 1/2" W x 19" H  
3" Thick

**UPHOLSTERY OPTIONS**

**STANDARD**



**ESD**



**BUILT TO ORDER**

Each chair is configured to your exact specifications – choice of arms, tilt, height range, base style, and glides/caster options.



Height Range	Base Style	Back Size	Seat Height Adjustment	Adjustment Mechanism	Footring	Standard Model #	ESD Model #	Cleanroom Class 100/ ISO 5 Model #	Cleanroom Class 1000/ ISO 6 Model #	Cleanroom Class 10000/ ISO7 Model #	ESD/CR Class 100/ ISO 5 Model #	ESD/CR Class 1000/ ISO 6 Model #	ESD/CR Class 10000/ ISO 7 Model #	
DESK	27" Black Nylon	Medium	17" – 22"	2 Way	-	6000M	-	-	-	-	-	-	-	
				3 Way	-	6001M	-	-	-	-	-	-	-	
				4 Way	-	6002M	-	-	-	-	-	-		
		Large	17" – 22"	Rocker	-	6003M	-	-	-	-	-	-	-	-
				2 Way	-	6000	-	-	-	-	-	-	-	
				3 Way	-	6001	-	-	-	-	-	-		
	27" Polished Aluminum	Medium	15 ½" – 21"	2 Way	-	9050M-S	9050M-E	9050M-C2	9050M-C3	9050M-C4	9050M-E2	9050M-E3	9050M-E4	
				3 Way	-	9051M-S	9051M-E	9051M-C2	9051M-C3	9051M-C4	9051M-E2	9051M-E3	9051M-E4	
				4 Way	-	9052M-S	9052M-E	9052M-C2	9052M-C3	9052M-C4	9052M-E2	9052M-E3	9052M-E4	
		Large	15 ½" – 21"	Rocker	-	9053M-S	-	-	-	-	-	-	-	
				2 Way	-	9050L-S	9050L-E	9050L-C2	9050L-C3	9050L-C4	9050L-E2	9050L-E3	9050L-E4	
				3 Way	-	9051L-S	9051L-E	9051L-C2	9051L-C3	9051L-C4	9051L-E2	9051L-E3	9051L-E4	
	Large	16 ½" – 22"	4 Way	-	9052L-S	9052L-E	9052L-C2	9052L-C3	9052L-C4	9052L-E2	9052L-E3	9052L-E4		
			4 Way	-	9052L-S	9052L-E	9052L-C2	9052L-C3	9052L-C4	9052L-E2	9052L-E3	9052L-E4		
			Rocker	-	9053L-S	-	-	-	-	-	-	-		
	MID	27" Black Nylon	Medium	20" – 27 ½"	2 Way	18" Adj Chrome	6300M	-	-	-	-	-	-	-
					3 Way	18" Adj Chrome	6301M	-	-	-	-	-	-	-
					4 Way	18" Adj Chrome	6302M	-	-	-	-	-	-	
Large			20" – 27 ½"	2 Way	18" Adj Chrome	6300	-	-	-	-	-	-	-	
				3 Way	18" Adj Chrome	6301	-	-	-	-	-	-	-	
				4 Way	18" Adj Chrome	6302	-	-	-	-	-	-		
27" Polished Aluminum		Medium	19" – 26 ½"	2 Way	20" Adj Chrome	9350M-S	9350M-E	9350M-C2	9350M-C3	9350M-C4	9350M-E2	9350M-E3	9350M-E4	
				3 Way	20" Adj Chrome	9351M-S	9351M-E	9351M-C2	9351M-C3	9351M-C4	9351M-E2	9351M-E3	9351M-E4	
				4 Way	20" Adj Chrome	9352M-S	9352M-E	9352M-C2	9352M-C3	9352M-C4	9352M-E2	9352M-E3	9352M-E4	
		Large	19" – 26 ½"	2 Way	20" Adj Chrome	9350L-S	9350L-E	9350L-C2	9350L-C3	9350L-C4	9350L-E2	9350L-E3	9350L-E4	
				3 Way	20" Adj Chrome	9351L-S	9351L-E	9351L-C2	9351L-C3	9351L-C4	9351L-E2	9351L-E3	9351L-E4	
				4 Way	20" Adj Chrome	9352L-S	9352L-E	9352L-C2	9352L-C3	9352L-C4	9352L-E2	9352L-E3	9352L-E4	
TALL	27" Black Nylon	Medium	24" – 34"	2 Way	18" Adj Chrome	6500M	-	-	-	-	-	-		
				3 Way	18" Adj Chrome	6501M	-	-	-	-	-	-		
				4 Way	18" Adj Chrome	6502M	-	-	-	-	-	-		
		Large	24" – 34"	2 Way	18" Adj Chrome	6500	-	-	-	-	-	-		
				3 Way	18" Adj Chrome	6501	-	-	-	-	-	-		
				4 Way	18" Adj Chrome	6502	-	-	-	-	-	-		
	27" Polished Aluminum	Medium	21 ½" – 31 ½"	2 Way	20" Adj Chrome	9550M-S	9550M-E	9550M-C2	9550M-C3	9550M-C4	9550M-E2	9550M-E3	9550M-E4	
				3 Way	20" Adj Chrome	9551M-S	9551M-E	9551M-C2	9551M-C3	9551M-C4	9551M-E2	9551M-E3	9551M-E4	
				4 Way	20" Adj Chrome	9552M-S	9552M-E	9552M-C2	9552M-C3	9552M-C4	9552M-E2	9552M-E3	9552M-E4	
		Large	21 ½" – 31 ½"	2 Way	20" Adj Chrome	9550L-S	9550L-E	9550L-C2	9550L-C3	9550L-C4	9550L-E2	9550L-E3	9550L-E4	
				3 Way	20" Adj Chrome	9551L-S	9551L-E	9551L-C2	9551L-C3	9551L-C4	9551L-E2	9551L-E3	9551L-E4	
				4 Way	20" Adj Chrome	9552L-S	9552L-E	9552L-C2	9552L-C3	9552L-C4	9552L-E2	9552L-E3	9552L-E4	

## ACCESSORIES

### ARMS



**A5**

Standard and CR Models



**A8**

ESD and ESD/CR Models

### CASTERS

Casters add 1" to seat height range.



### HARD FLOOR CASTERS

Standard: 3850S/5  
6000 only: 4550S/5  
ESD: CARD5S



### CARPET CASTERS

Standard: 3850/5  
6000 only: 4550/5  
ESD: CAPD5S



### SPECIALTY CASTERS

**INTERNAL BRAKING**  
Standard: IBCS  
ESD: IBCS-ESD

**REVERSE BRAKING**  
Standard: RBCS  
ESD: RBCS-ESD