

Specifications

Product Name	BB04 BitScope Blade Quattro Pi
Compatible Raspberry Pi Models	Raspberry Pi 3, 2, B+, A+ and Pi Zero
Supports Raspberry Pi Display	Yes (optional wall mount).
Raspberry Pi per Unit	4
USB Ports per Unit	16
HDMI & sound outputs	Yes (Raspberry Pi slot 1)
Primary Power	5V (Raspberry Pi J8 & USB)
Auxilliary Power	Yes (5V via header)
Indicator LEDs	Board Power & Devices Available
Device power-down header	Yes
Processor reset/interrupt	Yes
Blade mount tabs	Vcc & Gnd with M3 holes
Raspberry Pi mounts	M2.5 per HAT specification
Mounting feet included	Yes
19" rack compatible	7RU (with metalwork option)
DIN Rail compatible	Yes (with DIN rail option)
Power budget	4A (peak), 3A (continuous)
UPS compatible	Yes (includes blocking diode)
PoE compatible	Yes (with passive PoE cable)

Power Requirement	7V (4A) ~ 48 V (500mA)
Operating Temperature	0 °C to 40 °C
Storage Requirements	-40 °C ~ +40 °C / 5 % ~ 95 % RH
Dimensions (W x D x H)	65 x 280 x 25 mm
Weight (Net)	100g