

FEATURES

- EasyRail Plus Technology allowing plenty of wattage headroom to handle your devices
- Ultra Quiet Fan Design
- Ultra Voltage Regulation Design
- Haswell Ready
- AMD Radeon CrossFire Ready
- NVIDIA GeForce SLI Ready
- True Wattage guarantee
- 80 Plus Bronze
- Extreme heat tested capacitors

SPECIFICATIONS

- +12V Rail Outputs : Single
- 100% Tested and Verified : Y
- ATX12V 2.2 & ESP12V 2.91 Compliant : Y
- Maximum Wattage (W) : 750
- Modular Cables : Y
- Performance Category : Performance
- UPC Number : 778656057920
- CrossFire Ready : Y
- SLI Ready : Y
- AC Input Current (Arms) : 9A-4.5A
- AC Input Frequency (Hz) : 50/60 Hz
- AC Input Voltage (Vac) : 90-264
- Efficiency @ Typical Load : Up to 85%
- Energy-Efficiency : 80 Plus Bronze Certified
- High Reliable 105°C Japanese Capacitors : Y
- Solid State Capacitors : Y
- Tight voltage regulation ($\pm 5\%$) : Y
- Active Power Factor Correction (PFC) : Y
- Over Current Protection (OCP), Over Power Protection (OPP), Over Temperature Protection (OTP), Over Voltage Protection (OVP), Short Circuit Protection (SCP), Under Voltage Protection (UVP) : Y
- Cooling Fan Size (mm) : YES; 135mm Fluid dynamic Fan (Black)
- Package Dimensions (cm) : 32.3 x 21.1 x 14.2
- Package Dimensions (inch) : 13.7 x 8.3 x 5.6
- Package Weight (Kg) : 3.27 est.
- Package Weight (lb) : 7.21est
- PSU Dimension (cm) :
- PSU Dimension (inch) :
- Units per Carton : 4

CONNECTORS

- 1x 20+4-Pin ATX12V/EPS12V
- 1x 8-Pin EPS12V
- 1x 4+4-Pin ATX12V/EPS12V
- 4x 6+2-Pin-PCle
- 8x SATA
- 5x 4-Pin-Molex
- 1x Floppy
- Warranty: 5yr