


Capacitor, aluminum, 1000 uF, +/-20% Tol, -40/+85C, 450 VDC@85C



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	40	+1
L	80	+/-2
S	22.5	+/-0.1
LL	6.3	+/-1
F	2	+/-0.1

Notes:  
 -Dimensions D And L Include Sleaving

General Information	
Supplier:	KEMET
Application:	General Purpose
Part Type Description:	Snap-In, Aluminum Electrolytic
Lead Type:	4 Pin
Weight:	131 g
RoHS:	Yes

Specifications	
Capacitance:	1000 uF
Voltage:	450 VDC
Tolerance:	+/-20%
Voltage:	495 VDC (Surge)
Rated Temperature:	85C
Temperature Range:	-40/+85C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C)
Life:	29000 Hrs (Rated Voltgae At 85C)
Leakage Current:	2.7 mA
Leakage Condition:	uAmps (5min 20C)
Resistance/ESR:	114 mOhms (100Hz 20C)
Resistance/ESR:	75 mOhms (10kHz 20C)
Current/Ripple Current:	4.95 Amps (100Hz 85C)
Current/Ripple Current:	9.32 Amps (10kHz 85C)

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	25