


Capacitor, film, Metallized Paper, 0.047 uF, +/-20% Tol, -40/+110C, Safety: X1, 480 VAC, Lead Spacing=22.5 mm



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	27	MAX
H	17	MAX
T	8	MAX
S	22.5	+/-0.4
LL	30	+5
F	0.8	+/-0.05

**Packaging Specifications**

Package Kind:	Bulk
Package Quantity:	200

**General Information**

Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Safety: X1
Style:	Radial Molded
Lead Form:	Wire Leads
Features:	Pulse
Approvals:	ENEC
RoHS:	Yes

**Specifications**

Capacitance:	0.047 uF
Voltage:	1000 VDC
Tolerance:	+/-20%
Voltage AC:	480 VAC
Rated Temperature:	110C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	1000 v/us
Miscellaneous:	SRF= 6 MHz