

KEMET Part Number: PMR209ME6470M100R30
(P409EL474M250AH101)

Capacitor, film, Metallized Paper, 0.47 uF, +/-20% Tol, -40/+85C, Integrated Resistor (X2), 630 VDC@85C, Lead Spacing=25.4 mm, Not For New Design, Please Check Possible Alternative Parts (AltPart)



Dimensions (mm)

Symbol	Dimension	Tolerance
L	30.5	MAX
H	22	MAX
T	15.3	MAX
S	25.4	+/-0.4
LL	30	+5
F	1	+/-0.05

Packaging Specifications

Package Kind:	Bulk
Package Quantity:	75

General Information

Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Integrated Resistor (X2)
Style:	Radial Molded
Lead Form:	Wire Leads
Features:	Pulse
RoHS:	Yes

Specifications

Capacitance:	0.47 uF
Voltage:	630 VDC
Tolerance:	+/-20%
Voltage AC:	250 VAC
Rated Temperature:	85C
Temperature Range:	-40/+85C
Insulation Resistance:	2.13 GOhm
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart)
Miscellaneous:	Resistor= 100 Ohms