


**KEMET Part Number: C322C224M5U5TA**  
(C322C224M5U5TABULK)

Capacitor, ceramic, 0.22 uF, +/-20% Tol, 50 V, Z5U, Lead Spacing=0.2"



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	5.08	MAX
H	5.84	MAX
T	3.18	MAX
S	5.08	NOM
LL	7	MIN
F	0.51	NOM

**Packaging Specifications**

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500

**General Information**

Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	Z5U
Body Type:	Radial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

**Specifications**

Capacitance:	0.22 uF
Voltage:	50 V
Tolerance:	+/-20%
Temperature Range:	+10/+85C
Failure Rate:	N/A
Dissipation Factor:	4%
Insulation Resistance:	450 MOhm
Dielectric Strength:	125 V