


Capacitor, Ceramic, SMD, MLCC, FT-CAP, Ultra-Stable, Auto Grade, 0.015 uF, +/-5% Tol, 100 V, C0G, 0805 (2012 metric)



| General Information | |
|--------------------------|---|
| Supplier: | KEMET |
| Application: | Automotive (AEC-Q200 Qualified) |
| Chip Size: | 0805 (2012 metric) |
| Temperature Coefficient: | C0G |
| Part Type Description: | SMD, MLCC, FT-CAP, Ultra-Stable, Auto Grade |
| Termination Type: | Flexible Termination |
| Marked: | No |
| RoHS: | Yes |

| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| L | 2 | +/-0.3 |
| W | 1.25 | +/-0.3 |
| T | 1.25 | +/-0.15 |
| B | 0.5 | +/-0.25 |
| S | 0.75 | MIN |

| Specifications | |
|------------------------|---------------------|
| Capacitance: | 0.015 uF |
| Voltage: | 100 V |
| Tolerance: | +/-5% |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 0.1% |
| Failure Rate: | N/A |
| Aging Rate: | 0% loss/decade hour |
| Insulation Resistance: | 66.67 GOhm |
| Dielectric Strength: | 250 V |

| Packaging Specifications | |
|--------------------------|--------------|
| Package Kind: | T&R |
| Package Size: | 7 in/180 mm |
| Package Type: | Plastic Tape |
| Package Quantity: | 2500 |