


**KEMET Part Number: C114K103K5X5CA**  
(CK12BX103K)

Capacitor, ceramic, 0.01 uF, +/-10% Tol, 50 V, BX



Dimensions (in)		
Symbol	Dimension	Tolerance
D	0.09	+/-0.01
L	0.16	+/-0.01
LL	1.5	MIN
F	0.02	-0.003

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	200

General Information	
Supplier:	KEMET
Application:	MIL-PRF-11015
Temperature Coefficient:	BX
Body Type:	Axial Molded
Lead Type:	Wire Leads
Termination Type:	Tin-Lead (SnPb)
RoHS:	No

Specifications	
Capacitance:	0.01 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Failure Rate:	N/A
Dissipation Factor:	2.5%
Dielectric Strength:	125 V