


Capacitor, Tantalum, SMD, Molded, 100 uF, 6032, +/-10% Tol, 16 VDC (85C)



General Information	
Supplier:	KEMET
Brand:	evora
Application:	General Purpose
Part Type Description:	SMD, Molded
Construction:	Standard Chip-MnO2
Body Type:	SMD Chip
Footprint:	6032
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	6	+/-0.3
W	3.2	+/-0.3
H	2.5	+/-0.3
K	1.8	typ
F	2.2	+/-0.1
S	1.3	+/-0.3

Specifications	
Capacitance:	100 uF
Tolerance:	+/-10%
Voltage:	16 VDC (85C)
Voltage:	10.72 VDC (125C)
Temperature Range:	-55/+125C
Failure Rate:	N/A
Leakage Current:	16 uA
Dissipation Factor:	10%

Notes:

-Obsolete

-Old Part Number [Obsolete] Was B45196H3107K309

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	750