

RCP2500-AMP


General

| | |
|--------------|-------------|
| Style Number | RCP2500-AMP |
| Part Number | RCP2500-AMP |
| Product Code | 50007 |
| Availability | Custom |
| U Height | 2 |
| MIB | N/A |

Physical

| | |
|--------------------------------|---------------------------------|
| Dimensions (H x W x D, inches) | Box: 4 x 15 x 4 Unit: 0 x 0 x 0 |
| Mounting Style | Horizontal |

Output

| | |
|------------------|---|
| Outlets | (2) NEMA 5-15R  |
| Circuit Breakers | None |
| Outlet Control | No Remote Control |
| Local Switches | None |

Protection & Filtering

| | |
|-------------------------|------|
| Spike/Surge Suppression | Yes |
| EMI/RFI Filter | None |

Control & Interface

| | |
|--------------------|------|
| Serial Interface | No |
| Ethernet Interface | No |
| Voltage Monitoring | None |

* List Prices are not a reflection of the actual product Street Price. Check with your Eaton reseller or partner to get actual pricing.

[Privacy Policy](#)
[Terms & Conditions](#)
[Copyright](#)

© 2016 Eaton
All Rights Reserved