



WD Elements™

Portable Storage

Simple, fast and portable.



- Ultra-fast USB 3.0 interface
- Massive capacity
- Plug-and-play connectivity

WD Elements portable storage with USB 3.0 delivers maximum data transfer rates, universal connectivity and up to 3 TB capacity for value-conscious consumers who are looking for reliable, high-capacity storage to go. Protect your files with the free 30-day trial of WD SmartWare™ Pro and back up your files to your WD Elements drive or to your Dropbox™ account.





WD Elements

Portable Storage

Product Features



Maximum transfer rates

When connected to a USB 3.0 port, WD Elements portable storage delivers maximum performance for data transfers. Transfer a full-length HD movie in a fraction of the time it takes with USB 2.0.

Performance may vary based on user's hardware and system configuration.

USB 3.0 and USB 2.0 compatibility

Works seamlessly with the latest USB 3.0 devices and is backward compatible with USB 2.0 devices as well.

High capacity in a small enclosure

The small, lightweight design offers high-capacity storage, making WD Elements portable storage the ideal companion for value-conscious consumers who want to take their important files with them.

Free trial of WD SmartWare Pro backup software

WD Elements includes a free trial version of WD SmartWare Pro backup software. With it you can back up files to the local WD Elements drive or you can back up to the cloud using your Dropbox™ account.

Dropbox account required for cloud backup. Cloud services may be changed, terminated or interrupted at any time and may vary by country.

Improve PC performance

When your internal hard drive is almost full your PC slows down. Don't delete files. Free up space on your internal hard drive by transferring files to your WD Elements and get your PC moving again.

WD quality inside and out

We know your data is important to you. So we build the drive inside to our demanding requirements for durability, shock tolerance and long-term reliability. Then we protect the drive with a durable enclosure designed for style and protection.

Formatted for Windows®

Formatted NTFS and compatible with Windows 10, 8 and 7, Windows Vista®, Windows XP. Can be reformatted for Mac®.

Product Specifications

CAPACITIES AND MODELS

500 GB	WDBUZG5000ABK
1 TB	WDBUZG0010BBK
1.5 TB	WDBU6Y0015BBK
2 TB	WDBU6Y0020BBK
3TB	WDBU6Y0030BBK

500 GB AND 1 TB DIMENSIONS

Height:	0.60 in (15 mm)
Depth:	4.40 in (111 mm)
Width:	3.20 in (82 mm)
Weight:	0.30 lb (0.13 kg)

1.5TB, 2TB AND 3TB DIMENSIONS

Height:	0.82 in (21 mm)
Depth:	4.40 in (111 mm)
Width:	3.20 in (82 mm)
Weight:	0.51 lb (0.23 kg)

LIMITED WARRANTY

1 year	Americas
2 years	EMEA
3 years	APAC/Japan

KIT CONTENTS

Portable hard drive
USB cable
Quick Install Guide
Trial backup software launcher

OPERATING SPECIFICATIONS

Data transfer rate:¹
Up to 5 Gb/s with USB 3.0
Up to 480 Mb/s with USB 2.0
Operating temperature: 5°C to 35°C
Non-op. temperature: -20°C to 65°C

¹A certified USB 3.0 cable and interface are required to achieve USB 3.0 speeds.

SYSTEM COMPATIBILITY

Formatted NTFS for Windows 10, 8 and 7, Windows Vista®, Windows XP
Requires reformatting for Mac OS X

INTERFACE

USB 3.0



WD, the WD logo, and WD Elements are registered trademarks or trademarks of Western Digital Corporation or its affiliates in the U.S. and/or other countries. Other marks may be mentioned herein that are the property of their respective owners. Product specifications subject to change without notice. Pictures shown may vary from actual product. As used for storage capacity one terabyte (TB) = one trillion bytes. Total accessible capacity varies depending on operating environment.
© 2016 Western Digital Corporation or its affiliates