

Technical Specification

Input Devices - Mouse - Design&Features

Device Location:	External
Connectivity Technology:	Wired
Interface:	USB
Number of Buttons:	7
Button Function:	Programmable
Mouse Sensor:	Sunplus
Movement Resolution:	800 dpi
Max&Min Movement Resolution:	1600dpi 1200dpi 800dpi 2400dpi 4800dpi
DPI Adjustment Step:	400 dpi
Pointing Device Technology:	Optical
Mouse Features:	LED Backlight Braided cable with magnetic ferrite ring
Response Rate:	1000 Hz
Frame Rate:	6000 frames per second

Input Devices - Mouse - Miscellaneous

External Colour:	Black
Package Type:	Retail

Warranty and Logistic

Warranty

Warranty Products Returnable:	Yes
Warranty Term (month):	24 month(s)
Warranty Validation Criteria:	Serial Number

Logistic

Pack Length (mm):	196 mm
Pack Width (mm):	150 mm
Pack Height (mm):	56 mm
Pack Weight Brutto (kg):	0.26 kg
Pieces in pack:	1
Box Length (mm):	590 mm
Box Width (mm):	320 mm
Box Height (mm):	420 mm
Box Weight Brutto (kg):	11.5 kg
Packs in Box:	40
EAN Code:	5291485001261