

## Technical Specification

### Input Devices - Mouse - Design&Features

Device Location:	External
Connectivity Technology:	Wired
Interface:	USB
Number of Buttons:	6
Button Function:	Programmable
Max&Min Movement Resolution:	3500dpi 1500dpi 2000dpi 1000dpi 500dpi
Pointing Device Technology:	Optical
Mouse Features:	Blue Led Top cover with rubber coating
Max. Movement Speed:	60 in/sec
Maximum Acceleration:	20 G
Response Rate:	1000 Hz
Frame Rate:	3600 frames per second
Certifications:	CE, RoHS

### Input Devices - Mouse - Miscellaneous

External Colour:	Black
Included Accessories:	Gift Sticker
Package Style:	Premium carton box with magnet
Package Type:	Retail with hanger

### Input Devices - Mouse - Dimensions&Weight

Depth (mm):	125 mm
Height (mm):	38.5 mm
Width (mm):	68 mm
Weight Netto:	0.142 kg
Weight Brutto:	0.31 kg

## Warranty and Logistic

### Warranty

Warranty Products Returnable:	Yes
Warranty Term (month):	24 month(s)
Warranty Validation Criteria:	Serial Number

### Logistic

Pack Length (mm):	175 mm
Pack Width (mm):	215 mm
Pack Height (mm):	59 mm
Pack Weight Brutto (kg):	0.33 kg
Pieces in pack:	1
Box Length (mm):	365 mm
Box Width (mm):	330 mm
Box Height (mm):	455 mm
Box Weight Brutto (kg):	7.5 kg
Packs in Box:	20
EAN Code:	8717371864156