



## Harsh Environment Connectivity Solutions

---



Rear (0.250 mounting hole) and Front (0.469 mounting hole)  
Pushbutton Switches

These small momentary switches are completely enclosed in rugged metal housing. Front or rear-panel mount types offer 1-A, 1-B, 1-C, or 1-D switching. Red or black pushbuttons and solder terminals are standard.

---

## SPECIFICATIONS

**Body:** Copper alloy, plated.

**Pushbutton:** Molded red or black plastic, integral with shaft.

**Insulation:** Rigid plastic.

**Springs:** Integral contacts, plated.

Ratings: 250 mA, 30 W maximum, AC, non-inductive load.

**Solder Terminals:** Copper alloy, silver-plated.

**Locknuts:** Copper alloy, plated.

Series 903, 913: P-1053-1.

Series 923, 933: P-1150-1.

**Lockwasher:** Series 903, 913: Steel, P-1060-3

**Flat Washer:** Series 923, 933: Steel, plated,  
S-1790-1

## SPECIAL ORDER FEATURES

\* Other pushbutton colors.

\* Legends.

**PART NUMBERS**

Panel Mounting	Pushbutton Color/ Part Number		Circuit
	Red	Black	
Front	903	913	1-C
	*903D	*913D	1-D
Rear	923	933	1-C
	*923D	933D	1-D

\* Special order only; contact Switchcraft for price and delivery.