

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300570003](#)  
**Status:** **Active**  
**Overview:** Brad® Industrial Ethernet Solutions  
**Description:** Brad® RJ-Lnxx®, Threaded, RJ-45 Ethernet Field-Attachable Connector for Solid Core Cable

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">130057</a>
IP Rating	IP67
Overview	<a href="#">Brad® Industrial Ethernet Solutions</a>
Product Name	Brad®, RJ-Lnxx®
Type	Field Attachable Connector
UPC	78678842476

**Physical**

Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Polycarbonate
Material - Contact	Copper
Material - Coupling Nut	ABS
Material - Plating Mating	n/a
Net Weight	21.290/g
Orientation	Straight
Poles	N/A
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A

**Electrical**


Current - Maximum per Contact	4.0A
Voltage - Maximum	125V DC

**Material Info**

Old Part Number	ENSAM315
-----------------	----------

**Reference - Drawing Numbers**

Sales Drawing	SD-130057-002
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

**Search Parts in this Series**

[130057 Series](#)