

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0002091205**
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 4550, Female, with Tin (Sn) Plated Phosphor Bronze Contact, 14-20 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-43660-9999 \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	<u>4550</u>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Standard .093" Pin and Socket Connectors</u>
Packaging Alternative	<u>02-09-1206 (Loose)</u>
Product Name	Standard .093"
UPC	800753746084

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.330/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65-4.06mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm ²	N/A

Solder Process Data


Lead-free Process Capability N/A

Material Info

Old Part Number 4550-A(P901)

Reference - Drawing Numbers

Product Specification PS-02-09, PS-43660-9999
 Sales Drawing SD-4550-*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

4550 Series

Use With

1619 Plug or Receptacle Housing,
1545 Plug or Receptacle Housing, 1396
 Plug or Receptacle Housing, 1490 Plug
 or Receptacle Housing, 2629 Plug or
 Receptacle Crimp Housings, 1261 Plug or
 Receptacle Housing, 1292 Plug or Recept

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Insertion Tool	<u>0011020003</u>
Terminator Die	<u>0011402001</u>

Extractor Tool for .093 and HCS-125 Product Series	<u>0638240200</u>
Mini-Mac™ Applicator	<u>0638927100</u>
Mini-Mac™ Applicator	<u>0638927300</u>

This document was generated on 02/29/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION