

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0731713350](#)  
**Status:** **Active**  
**Overview:** [BNC RF Connectors](#)  
**Description:** 75 Ohms, BNC Right-Angle Jack with Low Profile Jam Nut, 3 Ghz

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	RF/Coax Connectors
Series	<a href="#">73171</a>
Comments	Optimized 3 GHz
Overview	<a href="#">BNC RF Connectors</a>
Product Name	BNC 3 GHz
Style	PCB
UPC	883906054861
Wire/Cable Type	N/A

**Physical**

Gender	Jack
Keying to Mating Part	Yes
Net Weight	10.316/g
Orientation	Right Angle
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.00mm
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
Reverse Polar	No

**Electrical**

Impedance	75#
-----------	-----

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	010
Lead-free Process Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-73171-335
---------------	--------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per -ED/79/2015 (17 December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

**Search Parts in this Series**

[73171](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**