

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0988171021](#)
Status: **Active**
Overview: NSCC - New Standard Casing Contact
Description: NSCC single part, Unsealed, 1.50mm, Female Housing, 3.33mm Pitch NSCC, Wire to Wire, 2 Circuits, Black

Documents:

[3D Model](#) [Application Specification AS-98821-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-98821-001 \(PDF\)](#)

General

Product Family Crimp Housings
 Series [98817](#)
 Application Power, Wire-to-Wire
 Application Tooling Part Link [63813-3800](#)
 Overview [NSCC - New Standard Casing Contact](#)
 Product Name NSCC
 UPC 822348761357

Physical

Breakaway No
 Circuits (maximum) 2
 Circuits Detail 2 x1.5mm female terminals
 Color - Resin Black
 Gender Female
 Glow-Wire Compliant No
 Keying to Mating Part Yes
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 1.640/g
 Number of Rows 1
 Packaging Type Carton
 Panel Mount No
 Pitch - Mating Interface 3.33mm
 Pitch - Termination Interface 3.33mm
 Polarized to Mating Part Yes
 Ports 1
 Temperature Range - Operating -40°C to +100°C

Electrical

Current - Maximum per Contact 10.0A

Solder Process Data


Lead-freeProcess Capability N/A

Material Info

Old Part Number 010009321

Reference - Drawing Numbers

Application Specification AS-98821-001
 Product Specification PS-98821-001
 Sales Drawing SD-98815-002, SD-98817-001



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Compliant

Search Parts in this Series

[98817 Series](#)

Mates With

[98822-1021](#) (Male Receptacle Housing)

Use With

Female Terminal NSCC [98897-1109](#) ,
[98897-1119](#) , [98897-1129](#) or FCI Female
 Terminal 1.5 Sicma 3

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extractor Tool for 0638133800
Unsealed Receptacle
Connectors

This document was generated on 03/29/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION