

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030384](#)
Status: **Active**
Overview: [Splices](#)
Description: Krimptite™ Temp-Term Butt Splice for 18-22 AWG Wire, 483°C (900° F), Loose Piece

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Splices
Series	19203
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	Krimptite™
UPC	822348424733

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel
Material - Plating Termination	Nickel
Net Weight	0.761/g
Packaging Type	Bag
Temperature Range - Operating	483°C
Wire Insulation Diameter	3.60mm
Wire Size AWG	18, 20, 22

Material Info

Reference - Drawing Numbers

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19203-015



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series
[19203 Series](#)