

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0368770003](#)
Status: **Active**
Overview: [Ditto™ Wire-to-Wire Interconnects](#)
Description: [Ditto™ Genderless Crimp Housing, Friction Lock, 3 Circuit](#)

Documents:

[3D Model](#) [Test Summary TS-36876-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-36876-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
 Series [36877](#)
 Application Wire-to-Wire
 Overview [Ditto™ Wire-to-Wire Interconnects](#)
 Product Name Ditto™
 UPC 887191583662


Physical

Circuits (maximum) 3
 Color - Resin Natural (White)
 Flammability 94V-0
 Gender Genderless
 Glow-Wire Compliant No
 Lock to Mating Part Yes
 Material - Resin Nylon
 Net Weight 0.900/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.50mm
 Pitch - Termination Interface 2.50mm
 Temperature Range - Operating -40°C to +105°C

Material Info

Reference - Drawing Numbers

Product Specification PS-36876-001
 Sales Drawing SD-36877-001
 Test Summary TS-36876-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
 -ED/79/2015 (17
 December 2015)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

[36877](#) Series

Mates With

Ditto™ Genderless Crimp Housing [36877](#)

Use With

Ditto™ Genderless Terminals [36876](#)