

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5600230421](#)  
**Status:** **Active**  
**Overview:** [Mini50™ Connection Systems](#)  
**Description:** CTX50 Receptacle Terminal, Unsealed, M-Grip, D-Wind, Left Payoff

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-560023-001 (PDF)</a>
<a href="#">Product Specification 5600230001 (PDF)</a>	<a href="#">Test Summary TS-560023-001 (PDF)</a>
<a href="#">Product Specification PS-560023-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<a href="#">560023</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini50™ Connection Systems</a>
Product Name	CTX50
UPC	884982134065

**Physical**

Durability (mating cycles max)	10
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.041/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.95-1.20mm
Wire Size AWG	N/A
Wire Size mm <sup>2</sup>	0.22

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	14V DC


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	<a href="#">AS-560023-001</a>
Product Specification	<a href="#">5600230001</a> , <a href="#">PS-560023-001</a>
Test Summary	<a href="#">TS-560023-001</a>



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Compliant

**Search Parts in this Series**

[560023](#) Series

**Use With**

[Mini50™ Unsealed Single Row Receptacle 34791](#) , [Mini50™ Unsealed Dual Row Receptacle 34824](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
FineAdjust™ Applicator for Receptacle Terminal Unsealed	<a href="#">0639014900</a>

Hand Crimp Tool for 0638230300  
Receptacle Terminal  
Unsealed

This document was generated on 03/08/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**