

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0193240003**  
**Status:** **Active**  
**Overview:** Metric Ring Terminals  
**Description:** Avikrimp™ Metric Ring Terminal for Stud Size 5-6 (M3-3.5), Insulated Barrel

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**Agency Certification**

UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series 19324  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview Metric Ring Terminals  
 Product Name Avikrimp™  
 Type Ring  
 UPC 887191290034

**Physical**

Barrel Type Closed - Brazed  
 Flammability 94V-2  
 Insulation Nylon (PA)  
 Material - Metal Copper Alloy  
 Material - Plating Mating Tin  
 Net Weight 0.747/g  
 Packaging Type Bag  
 Stud Size M3.5  
 Wire Size AWG N/A  
 Wire Size mm² 0.50-1.00

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Old Part Number AA1-832-M3,5

**Reference - Drawing Numbers**

Sales Drawing SD-19324-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
 -ED/79/2015 (17  
 December 2015)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

**Search Parts in this Series**

19324 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
PremiumGrade™ Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100