

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0193240015**
Status: **Active**
Overview: Metric Ring Terminals
Description: Avikrimp™ Metric Ring Terminal for Stud Size 5/16" (M8), Insulated Barrel

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series 19324
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview Metric Ring Terminals
 Product Name Avikrimp™
 Type Ring
 UPC 887191290157

Physical

Barrel Type Closed - Brazed
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 2.628/g
 Packaging Type Bag
 Stud Size 5/16" (M8)
 Wire Size AWG N/A
 Wire Size mm² 2.50-6.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Old Part Number C6-830-M8

Reference - Drawing Numbers

Sales Drawing SD-19324-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/108/2014 (17 Dec
 2014)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

19324 Series

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

| Description | Product # |
|--|------------|
| PremiumGrade™ Hand Crimp Tool | 0640010100 |
| Crimp Head for the AT-200™ Pneumatic Hand Tool | 0640050100 |