

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0193230006](#)  
**Status:** **Active**  
**Overview:** Metric Ring Terminals  
**Description:** VersaKrimp™ Metric Ring Terminal for Stud Size 5 (M3), Un-insulated

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E32244

**General**

Product Family Ring and Spade Terminals  
 Series [19323](#)  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Metric Ring Terminals](#)  
 Product Name VersaKrimp™  
 Type Ring  
 UPC 887191289205

**Physical**

Barrel Type Closed - Brazed  
 Insulation None  
 Material - Metal Copper Alloy  
 Material - Plating Mating Tin  
 Net Weight 0.546/g  
 Packaging Type Bag  
 Stud Size M3  
 Wire Size AWG N/A

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Old Part Number BB2,5-323-M3

**Reference - Drawing Numbers**

Sales Drawing SD-19323-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
 -ED/79/2015 (17  
 December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
 ELV

Green Image  
 Not Relevant

**Search Parts in this Series**

[19323](#) Series

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640070100</a>
PremiumGrade™ Hand Crimp Tool	<a href="#">0640030100</a>