

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193230013](#)
Status: **Active**
Overview: Metric Ring Terminals
Description: VersaKrimp™ Metric Ring Terminal for Stud Size 5 (M3), Un-insulated

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19323](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Metric Ring Terminals](#)
 Product Name VersaKrimp™
 Type Ring
 UPC 887191289977

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 1.401/g
 Packaging Type Bag
 Stud Size M5
 Wire Size AWG N/A
 Wire Size mm² 2.50-6.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Old Part Number C6-328-M5

Reference - Drawing Numbers

Sales Drawing SD-19323-001



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

Search Parts in this Series

[19323](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100
PremiumGrade™ Hand Crimp Tool	0640030100