


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0850840700](#)
Status: **Active**
Overview: SRC - Sealed Rectangular Connectors
Description: SRC Housing, Female, Hybrid 66 Pin Mixed Power and Signal (60 x MX150™ + 6 x MX150L™), Nylon, Black

Documents:

Drawing (PDF)	Application Specification 850830010 (PDF)
Product Specification 850700010 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 937320001 (PDF)	Product Literature (PDF)



General

Product Family	Crimp Housings
Series	85084
Application	Power, Signal, Wire-to-Wire
Comments	Polarized to mating part
Overview	SRC - Sealed Rectangular Connectors
Product Literature Order No	987650-7391
Product Name	SRC
UPC	883906945572

Physical

Circuits (maximum)	66
Circuits Detail	60 x MX150™ + 6 x MX150L™
Color - Resin	Black
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	106.910/g
Number of Rows	12
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	40.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	850830010
Product Specification	850700010, 937320001
Sales Drawing	850840700

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

85084 Series

Mates With

85083 SRC Power Blade Housing

Use With

33012 MX150™ Female Terminals. 19434 MX150L™ Female Terminal