

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0347970402](#)
Status: **Active**
Overview: MX150™ Unsealed Connector System
Description: MX150™ Cable Unsealed Male Connector with GM Style Clip, Single Row, 4 Circuits, Polarization B, Natural

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family	Crimp Housings
Series	34797
Application	Power, Wire-to-Wire
Comments	GM Clip Slot
Overview	MX150™ Unsealed Connector System
Polarization	B
Product Name	MX150™ Unsealed
UPC	884982970854

Physical

Circuits (maximum)	4
Color - Resin	Natural
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.360/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +105°C


Electrical

Current - Maximum per Contact	22.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-34797-001
---------------	--------------



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Not Relevant
Compliant

Search Parts in this Series

[34797](#) Series

Mates With

[34796](#) 3.50mm Pitch MX150™ Cable Unsealed Female

Use With

MX150™ Male Terminal [33000-0001](#) , [33000-0002](#) , [33000-0003](#) , [33000-1001](#) , [33000-1002](#) , [33000-1003](#)