

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0310671010](#)
Status: **Active**
Overview: H-DAC 64™ Unsealed Connector System
Description: 2.54mm H-DAC 64™, 3 Way Receptacle Assembly, Single Row, Polarization A

Documents:

[3D Model](#) [Application Specification AS-31067-100 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-31100-0001 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	31067
Application	Power, Wire-to-Board
Comments	Polarization Option A, Black
Overview	H-DAC 64™ Unsealed Connector System
Product Name	H-DAC 64™
UPC	800756063041

Physical

Circuits (maximum)	3
Color - Resin	Black, White
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	1.100/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +100°C

Electrical

Current - Maximum per Contact	11.0A, 9.0A
-------------------------------	-------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-31067-100
Product Specification	PS-31100-0001
Sales Drawing	SD-31109-003



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Compliant

Search Parts in this Series

[31067 Series](#)

Mates With

H-DAC 64™ 3 Way Male Housing Assembly
31067-1040 , 31067-1070

Use With

See Product Specification