

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301530242](#)  
**Status:** **Active**  
**Overview:** Ground Fault Circuit Interrupter (GFCI) Products  
**Description:** Super-Safeway® Fixed Mount Industrial GFCI, Permanent Mount, Multi Phase, Manual Reset, Flying Leads, 30A, 120/208V 3 Phase, 0.61m (2.0') Lead Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E66308

**General**

Product Family Power Distribution  
 Series [130153](#)  
 Enclosure Rating NEMA 6P  
 GFCI Reset Manual  
 Mounting Style Permanent  
 Open Neutral Relay Yes  
 Overview [Ground Fault Circuit Interrupter \(GFCI\) Products](#)  
 Product Name Super-Safeway™  
 Receptacle Type N/A  
 Type GFCI Industrial Duty, Multi-Phase  
 UPC 78172542943  
 Woodhead Yes

**Physical**

Cord Diameter N/A  
 Cord Grip Body Size N/A  
 Cord Length 0.61m (2.0')  
 Feed-Thru No  
 Flip Lid No  
 Material - Housing Nylon  
 Number of Receptacles 0  
 Packaging Type Carton

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 30.0A  
 GFCI Yes-In-line  
 Ground Continuity Monitor No  
 NEMA Configuration N/A  
 Voltage - Maximum 120V / 208V / 3 Phase

**Material Info**

Old Part Number 30053-2M5F

**Reference - Drawing Numbers**

Sales Drawing SD-130153-039



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

**Search Parts in this Series**

[130153](#) Series