

### General Information

|                        |   |
|------------------------|---|
| Extended Product Type: | JSM Orion02                                 |
| Product ID:            | 2TLA022310R1000                             |
| EAN:                   | 7350024482768                               |
| Catalog Description:   | JSM Orion02 -4 standard brackets for O3     |
| Long Description:      | JSM Orion02 -4 standard brackets for Orion3 |

### Categories

Products » Low Voltage Products and Systems » Control Products » Safety Products » Optical Safety Devices

### Ordering

|                         |               |
|-------------------------|---------------|
| EAN:                    | 7350024482768 |
| Minimum Order Quantity: | 1 piece       |
| Customs Tariff Number:  | 7326909890    |

### Dimensions

|                     |         |
|---------------------|---------|
| Product Net Height: | 45 mm   |
| Product Net Depth:  | 38 mm   |
| Product Net Weight: | 0.38 kg |

### Container Information

|                               |         |
|-------------------------------|---------|
| Package Level 1 Units:        | 1 piece |
| Package Level 1 Width:        | 150 mm  |
| Package Level 1 Height:       | 30 mm   |
| Package Level 1 Length:       | 180 mm  |
| Package Level 1 Gross Weight: | 0.38 kg |

### Additional Information

|                    |                              |
|--------------------|------------------------------|
| Product Main Type: | Orion Bracket                |
| Product Name:      | Mounting accessory           |
| Suitable For:      | Orion3 Base; Orion3 Extended |

### Certificates and Declarations (Document Number)

|                                    |          |
|------------------------------------|----------|
| Data Sheet, Technical Information: | N/A      |
| Declaration of Conformity - CE:    | NoDecNee |

### Classifications

|                             |   |
|-----------------------------|---|
| Object Classification Code: | U |
|-----------------------------|---|

