



Main

range of product	ClimaSys CC
range	ClimaSys
product or component type	Electronic hygrostat
product compatibility	Resistance heater
humidity setting range	20...80 %
display type	OLED screen
information displayed	Relative humidity

Complementary

input voltage	200...240 V AC
maximum switching capacity	4 A 230 V AC
electrical connection	6 terminals 2.5 mm ²
mounting mode	By screws Clipped
height	External : 85 mm
width	External : 56 mm
depth	External : 44 mm
mounting location	35 mm DIN rail Spacial upright On mounting plate Cross rails
ambient air temperature for operation	-40...80 °C
hysteresis	3 %
number of outputs	2 output(s) heating function
material	PC
colour	Light grey
flame retardance	Self-extinguishing conforming to UL94 (material V0)
product certifications	UR

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since ; 0940 - ; Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------