



**EAO AG**

Tannwaldstrasse 88  
4600 Olten  
Switzerland

**Phone:** +41 62 286 9111

[info@eao.com](mailto:info@eao.com)

## Part No. 45-190H.2000.111.101, Keylock Switch



[Specifications](#) | [Bill of Materials](#)

### Specifications

|                                     |   |
|-------------------------------------|---|
| <b>Actuator</b>                     | <u>Keylock switch</u>                   |
| <b>Lens Colour</b>                  | None                                    |
| <b>Function</b>                     | 2 Pos., maint., key release L/R (KL-KR) |
| <b>Housing Material</b>             | Metal                                   |
| <b>Shape of Handle or Frontring</b> | None                                    |
| <b>Lock System</b>                  | RONIS                                   |
| <b>Key</b>                          | T254                                    |
| <b>Key Type</b>                     | Standard Lock: Ronis T254               |
| <b>Switching Angle</b>              | 90 Grad (V-Pos)                         |
| <b>Contacts</b>                     | 1NO                                     |
| <b>Terminal</b>                     | Screw terminal                          |
| <b>Voltage Illumination</b>         | None                                    |

|  |                             |
|--|-----------------------------|
| <b>Mounting Type</b>                     | Front mounting              |
| <b>Mounting Style</b>                    | Holder                      |
| <b>Environmental Rating</b>              | IP66, IP67, IP69K           |
| <b>Industry Standards/Certifications</b> | UL, CSA, VDE, CCC, CE, RoHS |
| <b>Switching Function</b>                | On-Off                      |
| <b>Illumination</b>                      | None                        |
| <b>Contact Material</b>                  | Silver                      |
| <b>Termination Style</b>                 | Screw                       |
| <b>Mechanical Life</b>                   | 1'000'000 switching cycles  |
| <b>AC Voltage</b>                        | 500 V                       |
| <b>DC Voltage</b>                        | 500 V                       |
| <b>Switching Current</b>                 | 10 A                        |

Bill of Materials -

|                         |                  |
|-------------------------|------------------|
| <b>Actuator</b>         | 45-290H.2000.111 |
| <b>Holder</b>           | 45-2300.2000.000 |
| <b>Switch Element 1</b> | 45-311.1Z10      |