

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0002065102**  
**Status:** **Active**  
**Overview:** Standard .062" Pin and Socket Power Connectors  
**Description:** 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with 0.76µm Gold (Au) Plated Brass Contact, 18-24 AWG, Bag

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-1190-003 \(PDF\)](#)

**General**

|                         |   |
|-------------------------|---|
| Product Family          | Crimp Terminals                                       |
| Series                  | <u>1561</u>   |
| Application             | Power   |
| Crimp Quality Equipment | Yes   |
| Overview                | <u>Standard .062" Pin and Socket Power Connectors</u> |
| Packaging Alternative   | <u>02-06-5101 (Reel)</u>                              |
| Product Name            | Standard .062"  |
| UPC                     | 800754227582  |

**Physical**


|                                |                      |
|--------------------------------|----------------------|
| Gender                         | Female               |
| Material - Metal               | Brass                |
| Material - Plating Mating      | Gold                 |
| Material - Plating Termination | Nickel               |
| Net Weight                     | 0.080/g              |
| Packaging Type                 | Bag                  |
| Plating min - Mating           | 0.762µm              |
| Plating min - Termination      | 1.270µm              |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 1.52-3.05mm          |
| Wire Size AWG                  | 18, 20, 22, 24       |
| Wire Size mm <sup>2</sup>      | N/A                  |

**Material Info**

Old Part Number 1561-(P561)L

**Reference - Drawing Numbers**

Packaging Specification PK-1190-003  
 Sales Drawing SD-1561-\*



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
 -ED/79/2015 (17  
 December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
 ELV

Green Image  
 Not Relevant

**Search Parts in this Series**

1561 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description  | Product #         |
|--|-------------------|
| Hand Insertion Tool                                | <u>0011020001</u> |
| Hand Crimper - DISTRIBUTION ONLY                   | <u>0638111000</u> |
| Manual Extraction Tool                             | <u>0011030002</u> |
| Hand Crimp Tool for Standard 1.57mm Pin and Socket | <u>0638191300</u> |

This document was generated on 07/25/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**