

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191600024**
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 8 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-19408-109 \(PDF\)](#)
[Product Specification PS-19902-013 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Splices
Series [19160](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [Splices](#)
Product Name Closed-End Insulated
UPC 800753110298

Physical

Barrel Type Closed
Color - Resin Natural
Flammability 94V-2
Insulation Nylon (PA)
Material - Metal Copper
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 2.230/g
Packaging Type Bag
Temperature Range - Operating 105°C
Wire Insulation Diameter 12.19mm max.
Wire Size AWG 8

Electrical

Voltage - Maximum 600V

Material Info

Old Part Number NC-8

Reference - Drawing Numbers

Packaging Specification PK-19408-109
Product Specification PS-19902-013
Sales Drawing SD-19160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[19160 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the [Application Tooling
Specification document.](#)*

Global

Description	Product #
Hand Crimp Tool	0640012500
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640052500