

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0192150023**  
**Status:** **Active**  
**Overview:** Splices  
**Description:** Step Down Butt Splice for 10-16 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Splices  
 Series 19215  
 Comments Step down: 10/12 to 14/16 AWG  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview Splices  
 Product Name Butt - Step Down  
 UPC 800755062502

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 2.694/g  
 Packaging Type Bag  
 Temperature Range - Operating 149°C  
 Wire Insulation Diameter N/A  
 Wire Size AWG 10, 14, 16, 2  
 Wire Size mm<sup>2</sup> N/A

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Old Part Number CB-346

**Reference - Drawing Numbers**

Sales Drawing SD-19215-004



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
 ED/21/2016 (20 June  
 2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

**Search Parts in this Series**

19215 Series

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are  
 found by selecting the products below.  
 Crimp Height Specifications are then  
 contained in the Application Tooling  
 Specification document.*

**Global**

Description	Product #
PremiumGrade™ Hand Crimp Tool	<u>0640030100</u>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<u>0640070100</u>