



## Cordless Drill/Drivers

### **PSR 14,4**

Compact and powerful for all screwdriving work – with drill setting

[Go to product](#)



## Key product features

- Powerful 14.4 V motor with planetary gearbox
- 10 pre-selectable torque settings plus drill setting – optimum power for every application
- Twin-sleeve “Click” keyless chuck – easy, tool-free bit changes

## Other product advantages

- Bosch Electronic speed control: “accelerate” from 0 – max. using the trigger switch
- PowerLight – thanks to the built-in LED, your workpiece is always well lit and clearly visible
- Run-out brake and lock-off switch
- Quick-change battery pack
- Softgrip for a better and more comfortable hold
- Bit storage on the housing

## Comes complete with

- Charger
- 2 battery packs
- Plastic case (2 605 438 621)

**Part number:** 0603955471

**EAN code:** 3165140377218



Cordless Drill/Drivers

## **PSR 14,4**

### **Technical data**

---

**Battery voltage: 14,4 V**

**No-load speed: 0 – 700 rpm**

**Max. torque for soft/hard screw. applications: 12 / 28 Nm**

**Torque settings: 10 + 1**

**Drill chuck: Keyless chuck**

**Machine weight with battery: 1,5 kg**

#### **Screw diameter**

**Screw diameter up to: 8 mm**

#### **Drilling diameter**

**Drilling diameter in steel: 10 mm**

**Drilling diameter in wood: 25 mm**

### **Noise / vibration information**

---

Measured values determined according to EN 60745.  
Total vibration values (vector sum of three directions).

#### **Drilling in metal**

**Vibration emission value ah: 2.5 m/s<sup>2</sup>**

**Uncertainty K: 1.5 m/s<sup>2</sup>**

#### **Screwdriving**

**Vibration emission value ah: 2.5 m/s<sup>2</sup>**

**Uncertainty K: 1.5 m/s<sup>2</sup>**

The A-rated noise level of the power tool is typically as follows: Sound pressure level 75 dB(A); Sound power level 80 dB(A). Uncertainty K= 3 dB.

### **Functions**

---



**Battery voltage**

14.4 volts



### **Battery runtime**

Screwdriving performance with one battery charge



### **Keyless chuck**

Fast bit changes due to automatic spindle lock



### **Area of application**

Screwdriving / drilling



### **Integrated work light**

Optimum view of the workpiece

## **Functions**

---

14.4 Volt

Application: screwdriving / drilling

Softgrip

Integrated work light

Bosch Electronic

Right-hand/left-hand rotation