

# Product data sheet

## Characteristics

# 2601AG2

## DRUM SWITCH 600VAC 2HP A +OPTIONS

Product availability: Stock - Normally stocked in distribution facility

Price\*: 158.00 USD

### Main

Commercial Status	Commercialised
Product or component type	Reversing Drum Switch
NEMA degree of protection	NEMA 1
Motor power hp	0.25 hp 230 V DC 0.25 hp 115 V DC 2 hp 575 V AC 2 hp 460 V AC 2 hp 230 V AC 2 hp 200 V AC 2 hp 230 V AC 1.5 hp 115 V AC
[Ue] rated operational voltage	250 V DC 600 V AC
Poles description	3P

### Complementary

Product certifications	CSA UL listed
Electrical connection	Screw-clamp terminals
Range of product	A

### Ordering and shipping details

Category	21116 - 2601
Discount Schedule	CP1
GTIN	00785901555414
Nbr. of units in pkg.	1
Package weight(Lbs)	1.35
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein. \*Prices are indicative