

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0350211301](#)
Status: **Active**
Description: 2.00/2.50mm Board-In Terminal, Right Angle , Phosphor Bronze, Pre-Plated

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	35021
Application	Signal
Crimp Quality Equipment	Yes
Product Name	Board-In
UPC	800753576933


Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.028/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.50mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm ²	N/A

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-35021-001
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[35021](#) Series

Use With

[35023](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Hand Crimp Tool for Right Angle Board-In Crimp Terminals FineAdjust™ Applicator for Right Angle 2.00mm	0638116900 0639029000

(.079") Board-in-
Terminals
T2 Terminator for 0639129000
Right Angle, 2.00mm
(.079") Board-In
Terminals

This document was generated on 07/11/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION