

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191930201](#)
Status: **Active**
Description: RING VERSAKRIMP TAPED (D-356-08T)

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19193](#)
 Crimp Quality Equipment Yes
 Product Family Ring and Spade Terminals
 UPC 800753039803

Physical


Net Weight 2.916/g

Material Info

Old Part Number D-356-08T

Reference - Drawing Numbers

Sales Drawing SD-19193-012



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

[19193 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for VersaKrimp™ High Temperature Nickel Plated Steel Terminals on Tape, 8 AWG	0190270105
ATP Crimp Dies for VersaKrimp™ Copper Ring Tongue Terminals and Butt	0190472000

Splices on Tape, 8
AWG, use with Tape
Crimp Module and
ATP-201 Press
ATP Crimp Dies 0190270111
for VersaKrimp™
Copper Ring Tongue
Terminals And Butt
Splices on Tape, 8
AWG
ATP Crimp Dies for 0190270117
VersaKrimp™ Ring
Tongue Terminals,
for Solid Copper
or Steel Wire (Anti
Rotation)
ATP Crimp Dies 0190270120
for Versakrimp™ 8
AWG Ring Tongue
Terminals, for
Stripped Magnet or
Steel 6 AWG Wire

This document was generated on 07/13/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION