

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030099](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: VersaKrimp™ Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19203](#)
 Comments 650° F (343° C)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [High-Temperature Temp Terms Terminals and Splices](#)
 Product Name Temp-Terms, VersaKrimp™
 Type Ring
 UPC 800755059519

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Plating Mating Nickel
 Net Weight 1.480/g
 Packaging Type Bag
 Stud Size 10 (M5)
 Wire Size AWG 10, 12
 Wire Size mm² 4.00-6.00

Material Info

Old Part Number C-T-328-10

Reference - Drawing Numbers

Sales Drawing CTCD30101



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Not Relevant

Search Parts in this Series

[19203 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade™	0640030100
Hand Crimp Tool	
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640070100