

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0015311042](#)  
**Status:** **Active**  
**Description:** 4.80mm Pitch Wire-to-Wire Receptacle Housing, 4 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-5025-003 (PDF)</a>
<a href="#">Product Specification PS-5025-001 (PDF)</a>	<a href="#">Packaging Specification SPK-5025-001 (PDF)</a>
<a href="#">Product Specification PS-5025-002 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">5025</a>
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753604575

**Physical**

Circuits (maximum)	4
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Net Weight	1824.500/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Temperature Range - Operating	-40°C to +105°C

**Material Info**

Old Part Number	5025-04R1
-----------------	-----------

**Reference - Drawing Numbers**

Packaging Specification	SPK-5025-001
Product Specification	PS-5025-001, PS-5025-002, PS-5025-003
Sales Drawing	SD-5025-04R1

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[5025](#) Series

**Mates With**

[5025](#) Plug

**Use With**

[5005](#)