



Pin spacing: 5.75 mm / 0.226 in. 4 x 0.5 ... 1.0 mm Ø 4 x 24 ... 18 AWG 320 V/4 kV/2 6 A 150 V/7 A		Pin spacing: 5.75 mm / 0.226 in. 4 x 0.5 ... 1.0 mm Ø 4 x 24 ... 18 AWG 320 V/4 kV/2 6 A 150 V/7 A		Solder pins
---	--	---	--	--------------------



Color	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit	Item No.	Pack. Unit
4-conductor modular PCB connector, can be assembled to connector strips via dovetail joints, with test slot, for solid conductors			4-conductor PCB connector strip, with test slots, for solid conductors, light green			Solder pin for PCBs	
● gray	243-721	400	2	243-742	50	243-131	1000
● blue	243-722	400	3	243-743	50		
● orange	243-723	400	4	243-744	50		
● light green	243-724	400	5	243-745	50		
			6	243-746	50		
			7	243-747	50		
			8	243-748	50		
			Note: To limit the insertion forces of multi-pole PCB connector strips to the solder pins, the pole no. of the assembly should not exceed 8.				
			PCB terminal strips in other colors are available upon request (depending on quantity required):				
			● blue ● gray ● orange				