



0.14 ... 1 (1.5) mm² ① AWG 24 ... 16
500 V/6 kV/3 ② 600 V, 10 A ③
I_N 13.5 A (16 A)
Terminal block width 3.5 mm / 0.138 in.
9 ... 11 mm / 0.39 in. ③



Double-deck terminal block assembly
A double-deck marker carrier can be fitted retrospectively to double-deck terminal blocks without marker carrier.

- ① Conductor sizes: 0.14 mm² ... 1.5 mm² "s + f-st";
Push-in conductor sizes: 0.5 mm² ... 1.5 mm² "s"
and 0.5 mm² ... 0.75 mm²
"insulated ferrule, 10 mm"
- ② 500 V = rated voltage
6 kV = rated surge voltage
3 = pollution degree
(see Section 14)
- ③ Strip length, see packaging or instructions.
- ④ See application notes for:
Colored push-in type jumper bars, page 101
Vertical jumper, page 105

Item No.	Pack. Unit	2000 Series Accessories					
Shield conductor/through terminal block, with marker carrier,		Appropriate marking systems: WMB/Marking strips (see Section 13)					
gray housing		End and intermediate plate, 0.7 mm thick	Test plug adapter,				
○ Shield/N	2000-2248	orange	2000-2292	25	for 4 mm Ø test plug		
○ Shield/L	2000-2258	gray	2000-2291	25	gray	2009-174	100 (4x25)
Shield conductor/through terminal block, without marker carrier,		Push-in type jumper bar, insulated,	Banana plug,				
gray housing		④ I _N 14 A,	for socket 4 mm Ø,				
○ Shield/N	2000-2218	light gray	color mixed	215-111	50		
○ Shield/L	2000-2228	2-way	2000-402	200 (8x25)	Testing tap,		
		3-way	2000-403	200 (8x25)	for max. 2.5 mm ²		
		4-way	2000-404	200 (8x25)	gray	2009-182	100 (4x25)
		5-way	2000-405	100 (4x25)			
		6-way	2000-406	100 (4x25)			
		7-way	2000-407	100 (4x25)			
		8-way	2000-408	100 (4x25)			
		9-way	2000-409	100 (4x25)			
		10-way	2000-410	100 (4x25)			
		Push-in type jumper bar, insulated,					
		I _N 14 A,					
		light gray					
		from 1 to 3	2000-433	200 (8x25)			
		from 1 to 4	2000-434	200 (8x25)			
		from 1 to 5	2000-435	100 (4x25)			
		from 1 to 6	2000-436	100 (4x25)			
		from 1 to 7	2000-437	100 (4x25)			
		from 1 to 8	2000-438	100 (4x25)			
		from 1 to 9	2000-439	100 (4x25)			
		from 1 to 10	2000-440	100 (4x25)			
		Double-deck vertical jumper, insulated,					
		④ I _N 13.5 A					
		light gray	2000-492	100 (4x25)			
		Protective warning marker,					
		with high-voltage symbol, black,					
		for 5 terminal blocks					
		yellow	2000-115	100 (4x25)			
		Double-deck marker carrier,					
		pivoting					
		gray	2000-121	50 (2x25)			
		WMB Multi marking system,					
		10 strips with 10 markers per card,					
		for 3.5 mm terminal block width					
		plain	793-3501	5			
		Marking strip, plain,					
		11 mm wide,					
		50 m roll					
		white	2009-110	1			