

Microscope Lighting/Digital Options

LFOLED40

Old item no.: LFOLED40



80W LED ILLUMINATOR W/DIMMER

The LED Fiber Optic Illuminator features a dimmable 80W energy-efficient LED lightsource with 5000°K color temperature and 80 CRI. It produces 3250 footcandles at 4.5" working distance making it comparable to accessory LED ring lights. The LED Fiber Optic Illuminator can be positioned conventionally on the worksurface or in a vertical position to occupy an even smaller footprint.



Dimensions

Net weight (kg)	0
Gross weight (lb.)	7

Lightsource

Lamp power (W)	80
----------------	----

Body

Body color	Black
------------	-------