

CLIFF


MAINS INLET SOCKETS



CL19192 - MS1X/S SNAP-IN, UP TO 2.1mm PANEL,
0.5mm THK SOLDER TAGS




CL19193 - MS1X/A1 SNAP IN, UP TO 1.1mm PANEL,
1/4" FASTONS




CL191930 - MS1X/A1 SNAP IN, 2 POLE, UP TO 1.1mm
PANEL, 1/4" FASTONS




CL19192RB - MS1/X SNAP-IN, 1.5mm PANEL,
6.3mm FASTONS



CL19268 - FUSED MAINS INLET SOCKET XMS3,
1/4" FASTONS (4 TAGS), SELFTAP SCREWS



CL1927RB - FUSED MAINS INLET SOCKET MS3, 4.8mm
FASTONS (3 TAGS) WITH CAPTIVE FUSEHOLDER



CL19274 - FUSE CARRIER FOR MS3 230V/115V