



General ordering data

Order No.	1579060000
Part designation	WQB B/24
Version	Cross-connector / link for modular terminal, Cross-connection bridge, No. of poles: 24
EAN	4008190188597
Qty	20 pc(s).

Additional technical data

Explosion-tested version "Ex e"	No
---------------------------------	----

Cross-connector

Height	12 mm
No. of cross-connected terminals	24
Pitch	5.1 mm
Rated current, multi-pole	24 A
Rated voltage	0 V
Type	Cross-connector
Type of fixing	screwed
Function	Cross-connection bridge
No. of poles	24

Rating data

Rated voltage	0 V
---------------	-----

Downloads

DXF	18599_WQB_B-24_DXF.dxf
STEP	1579060000_18599_WQB_B-24_STP.stp

Classifications

ETIM 2.0	EC000489
ETIM 3.0	EC000489
eClass 4.1	27-14-11-99
eClass 5.0	27-14-11-40
eClass 5.1	27-14-11-40

Classifications

Similar products

Order No.	Part designation	Version
1579020000	WQB B/3	Cross-connector / link for modular terminal, Cross-connection bridge, No. of poles: 3
1579040000	WQB B/6	Cross-connector / link for modular terminal, Cross-connection bridge, No. of poles: 6
1579060000	WQB B/24	Cross-connector / link for modular terminal, Cross-connection bridge, No. of poles: 24
1579050000	WQB B/10	Cross-connector / link for modular terminal, Cross-connection bridge, No. of poles: 10
1579030000	WQB B/4	Cross-connector / link for modular terminal, Cross-connection bridge, No. of poles: 4
1579010000	WQB B/2	Cross-connector / link for modular terminal, Cross-connection bridge, No. of poles: 2